




REV	ECN	DESCRIPTION	DATE	MODIFIED
A		PRE-RELEASE	03-08-14	JACK.D


LEVER IN

锁紧后手柄位置

激光印字区




激光印字随熔断器规格变化, 如①表格内容。




详细组装图纸规格参数参照: MSD-ASSEMBLING

FUSE 熔断器规格	200A	250A	315A	350A 建议使用	400A	450A	500A	550A 建议使用	630A	SHUNT 铜棒
MARKING 印字(熔断器规格)	200A	250A	315A	350A	400A	450A	500A	550A	630A	SHUNT



LEVER IN
PRE-STAGE POSITION
预紧时手柄位置



NOTES:

- 1.INNER HOUSING MAY BE ASSEMBLED ROTATED 180° FROM AS SHOW
- 2.SHUNT MEANS NO FUSE USE TENMMA'S DIRECTLY
- 3.合上锁死后, 防水防尘等级IP67
- 4.使用方式详见MSD操作说明文件

DIMENSIONS	TOLERANCES	PROJECTION	TITLE	
ANSI Y14.5M UNITS: MM P/o/E FILE	.X .XX ANGLES ±1	±0.75 ±0.5	Amphenol Pcd Shenzhen	MSD PLUG ASSEMBLY
ORIGINAL NOT FOR CUSTOMER DISTRIBUTION	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD SHENZHEN	CHKD ENGR JACK.D	SIZE A3	DWG NO. MSD-M-XXXX
			CODE: 58982	SCALE: 35
			SHEET 1	OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MSDM5002](#) [MSDM4502](#) [MSDM6302](#) [MSDM3502](#) [MSDM000](#) [MSDM2002](#) [MSDM2502](#) [MSDM3152](#) [MSDM4002](#)
[MSDM5502](#)