






DIMENSION	
Dim A	$N/3 \times 5.08$
Dim B	$(N/3 - 1) \times 5.08$

N=Number of poles

Poles	Dim A	Dim B
3×2pole~3×6pole	±0.15	±0.15
3×7pole~3×12pole	±0.25	±0.25
3×13pole~3×18pole	±0.35	±0.35
3×19pole~3×24pole	±0.40	±0.40

No. of poles	0	Black (RAL9005)	0000 Standard @ Logo
06 3x2P POLES	5	Green(RAL6018/T)	000A Standard ANY Logo
09 3x3P POLES	6	Blue (RAL5015/A)	Any special item by
	8	Grey(RAL7035/D)	customer request,
72 3x24P POLES	C	Green(RAL6018/U)	please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YH 5.08mm Series 3x2P-3x24P (Without Cover)			
PART NO.		YHxx21x1xxxxG		DWG NO.	8YH0001
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Guoxue 2014.02.12	Guoxue 2014.02.12		UNIT: mm X. ±0.50
					SCALE: NONE X.X ±0.30
					REV.: E X.XX ±0.10
				SHEET: 01/01	X° ±1.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>YH0621510000G</u>	<u>YH0921510000G</u>	<u>YH1221510000G</u>	<u>YH1521510000G</u>	<u>YH1821510000G</u>	<u>YH2121510000G</u>
<u>YH2421510000G</u>	<u>YH2721510000G</u>	<u>YH3021510000G</u>	<u>YH3321510000G</u>	<u>YH3621510000G</u>	<u>YH3921510000G</u>
<u>YH4221510000G</u>	<u>YH4521510000G</u>	<u>YH4821510000G</u>	<u>YH5121510000G</u>	<u>YH5421510000G</u>	<u>YH5721510000G</u>
<u>YH6021510000G</u>	<u>YH6321510000G</u>	<u>YH6621510000G</u>	<u>YH6921510000G</u>	<u>YH7221510000G</u>	<u>YH0621810000G</u>
<u>YH0621610000G</u>	<u>YH0621610060G</u>	<u>YH0621610070G</u>	<u>YH0621810060G</u>	<u>YH0621810070G</u>	<u>YH0621510060G</u>