



FCI CONFIDENTIAL

FCI

This document is the property of FCI and contains CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI.
Copyright FCI


FCIconnect.com

PRODUCT No.
10079074-001LF




NOTES:

1. 100% CONTINUITY TEST FOR OPEN, SHORTING, ETC..
2. WIRES SOLDERED DIRECTLY TO PCB.
3. MAKE SURE THE CONTACT ORIENTATION, SEE DETAIL B.
4. OUTER CABLES HAVE TO BE 2MM LONGER THAN INNER CABLES.
5. PCB THICKNESS 1.8MM(REF).
6. ROHS COMPLIANCE.



DETAIL A SCALE 4:1



DETAIL B SCALE 2:1

FCI P/N	ERICSSON P/N
10079074-001LF	SXK1115156/1

mat'l. code		surface	tolerance	projection	product family
		ISO 1302	ISO 406 ISO 1101		
ltr	ecn no	dr	date	tolerances unless otherwise specified	
A	N07-0207	ST	8/30/07	title	
B	001-1115156-1	ST	4/8/13	ERICSSON Power PBA	
		angles	linear	±1.0	
		±2'		scale	
		dr	Sunny Tsai	10JUL07	
		engr	Sunny Tsai	10JUL07	
		chr	Jackson Wang	10JUL07	
		appa	Jackson Wang	10JUL07	
sheet	revision	B			
index	sheet	1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10079074-001LF](#)