



RECOMMENDED PCB Pattern

(Tolerance : ±0.05)

-NOTE-

1. This product is enable to mount both USB-IF Recommended PCB pattern and NEW USB-IF Recommended PCB Pattern
2. Coplanarity : The dimension between flat tool and when connector put on the flat tool like PCB botton of soldering terminals
Signal terminal / Metal (front) : Max 0.08 mm
3. PRODUCT NUMBERING
10103594 - 0001 LF

No.	Part Name	Material	Finish	Remarks
1	Socket Housing	Thermoplastic	(Black)	
2	Socket Contact Ter	Copper Alloy	Au over Ni	
3	Socket Shield	Stainless Steel	Sn over Ni	
4	Socket Plate	Stainless Steel		

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		 www.fciconnect.com		
ltr	ecn no	dr	date	linear	.X ± 0.38		projection	title			
A	T10-0002	J.H	1/7/10		.XX ± 0.25			MICRO-USB B-TYPE RECEP.			
					.XXX ± 0.15						
				angles	0° ±2°						
				dr	JASON HSU	1/7/10	MM	product family USB		code	
				enr	JASON HSU	1/7/10		size dwg no		TWN	
				chr	GARY HSIEH	1/7/10		scale	A4		sheet
				appd	JOSEPH HSIA	1/7/10			NA		1 of 1
sheet index	revision sheet	A	1								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10103594-0001LF](#)