



Copyright FCI.

FCI	DESCRIPTION
	10104319-001RLF
	10104319-003RLF
	10104319-009RLF







A

B

C

D



NOTES:

1. MATERIAL: BERYLLIUM COPPER ALLOY.

2. CONTACT PLATING:

CONTACT AREA: PLATING 1um Au over 1.0/3.0 um Ni UNDERPLATE.

or PLATING 0.05 to 0.15um Au over 1.0/3.0 um Ni UNDERPLATE.

△ or PLATING 1um GXT over 1.0/3.0 um Ni UNDERPLATE.

(1um GXT is 0.025~0.125um Au over 0.875um PdNi)

SOLDER AREA: PLATING 0.05 to 0.15um Au over 1.0/3.0um Ni UNDERPLATE.

3. PACKAGING: TAPE & REEL

4. PART NUMBER DESCRIPTION:

10104319-0 0 X X X

LF: LEAD FREE

R: TAPE AND REEL

CONTACT PLATING

1: 1um Au over Ni.

△ 3: 0.05~0.15um Au over Ni.

9: 1um GXT over Ni.

rev	ecn no	dr	date
A	DG09-0331	NZ	2009-11-09
B	DG11-0048	SM	2011-02-22
C	ELX-DG-011079-1	ANDY	2012-03-27
-	-	-	-
-	-	-	-

spec ref		*		dr	Louis Ng	2009/10/06	projection 	mm 	size	A4	scale	16.000
tolerance std ASME Y14.5	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Andy Lu	2012/03/27			ecn no	ELX-DG-011079-1		
				chr	Young Ou	2012/03/28						
				appr	Pei-Ming Zheng	2012/03/28	product family		-	rel level Released		
surface - 	linear	0.X	±0.3		title	ANTENNA CONNECTOR UNIVERSAL CONTACT			dwg no	10104319		rev C
		0.XX	±0.15									
		0.XXX	±0.050									
ASME Y14.5	angular	0°	±2°	www.fci.com	cat. no.	10076429	Product - Customer Drw			sheet 1 of 1		

Print File - REV C - 2009-06-09

2

3

PDS: Rev :C

STATUS:Released

Printed: Mar 28, 2012

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10104319-009RLF](#) [10104319-001RLF](#)