


FCI P/N	L (MM)
10127220-R0011YYLF	109±3



(A) 10 MM STRIPPED AND KEEP THE INSULATION ON THE END.

NOTES:

1. PART NUMBER SCHEME FOR CABLE ASSEMBLY:

10127220-R0011YYLF

Lead Free
 NOT APPLICABLE TO THIS ASS'Y
 LENGTH: (METRERS & CENTIMETERS)
 0011: 0 METER 11 CENTIMETERS
 WIRE GAUGE
 R: 30AWG

2. ROHS COMPLIANCE

②	WIRE	UL1007 30AWG,Tinned copper, White				A/R	M	
①	TERMINAL	WTB 1.25MM PITCH TERMINAL				1	EA	
No.	PART	DESCRIPTION				QTY	UNIT	
www.fciconnect.com		surface - ✓		tolerance std - -		projection 	mm 	
		TOLERANCES UNLESS OTHERWISE SPECIFIED						
Dr	Harry Shi	2014-01-08	ANGULAR	LINEAR	0.X	±-	size A4	Scale 3:1
Eng	Harry Shi	2014-01-08			0.XX	±-		
Chr	Harry Shi	2014-01-08			0° ±°	0.XXX		
Appr	Jackson Wang	2014-01-08	Product family			ECN		-
		title Wire with the terminal			dwg no 10127220		Rev. A	
		catalog no -			CUSTOMER		sheet 1 of 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10127220-R0011YYLF](#)