


FCI P/N	L/mm
10129479-P0006YYLF	60



NOTES:

1.TEST:

D/S:100% TEST.
CONNECTION RESISTANCE: 3 OHM MAX.
HI-POT:300V/10mS.
INSULATION RESISTANCE: 10 MOHM MIN.

2. ROHS COMPLIANCE

3. LABEL DETAIL

P/N: 995630X2
LOT: FFYYWW
MADE IN XXXX

Where: XXXX
FF=Factory symbol
YY=year
WW=week

XXXX=Country of origin

Font type: Arial or Univers 57 Condensed
Font size: Human readable (minimum heigh 1,5 mm)

rev	ecn no	dr	date
A		Harry	2014-05-29

spec ref	See Notes		
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED		
surface	linear	0.X	±
		0.XX	± 0.20
		0.XXX	±
	angular	0°	±°

③	LABEL	LABEL . W=25MM		1	EA
②	IDC CONN.	Minitex 2x4 position IDC receptacle, 0.76um gold, with central key and friction latch bump,		2	EA
①	RIBBON CABLE	UL2651, 28AWGx8C, Pitch1.0, Grey PVC		A/R	M
No.	NAME	DESCRIPTION		QTY	UNIT
dr	Harry Shi	2014-05-29	projection	MM	size A3 scale N/A
eng	Harry Shi	2014-05-29		ecn no	
chr	Guo-Feng Jin	2014-05-29		rel level	
appr	Guo-Feng Jin	2014-05-29			
		product family	Quickie IDC		
		QUICKIE IDC CABLE ASSEMBLY		dwg no 10129479-P0006YYLF	
www.fci.com		cat. no.		Product - Customer Drw	
				sheet 1 of 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10129479-P0006YYLF](#)