

1

2

3

4

A

B

C


D

A

B

C

D



## NOTES:

## 1. TEST:

Q/S:100% TEST.  
CONNECTION RESISTANCE: 3 Ohm MAX.  
HI-POT:300V/10mS.  
INSULATION RESISTANCE: 10M Ohm MIN.

## 2. ROHS COMPLIANCE

②	MINITEK 2*25 POSITION IDC RECEPTACLE, 2.0MM PITCH WITH CENTER KEY.	2	PC
①	FLAT CABLE UL2651,28AWG*50C, PITCH 1.0MM.	AR	M
No.	DESCRIPTION	QTY	UNIT
	projection	size	scale
	MM	A3	N/A
	ecn no		
	rel level		
	product family	Quickie IDC	
	title	QUICKIE IDC CABLE ASSEMBLY	rev
	cat. no.	www.fci.com	A
	Product - Customer Drw	sheet 1 of 1	

spec ref	See Notes	dr	Harry Shi	2014-04-03
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	Harry Shi	2014-04-03
		chr	Guo-Feng Jin	2014-04-03
		appr	Johnson Long	2014-04-03
surface	linear	0.X	±	
		0.XX	± 0.20	
		0.XXX	±	
	angular	0°	±°	

rev	ecn no	dr	date
A		Harry	2014-04-02

Pro/E File - REV C - 2009-06-09

1

2

3

4

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10129542-P0013YYLF](#)