





spec ref				dr		Jeny Ren	2017/11/01		projection				MM		size		A3	scale		2:1															
tolerance std ASME Y14.5				TOLERANCES UNLESS OTHERWISE SPECIFIED								eng		Jeny Ren		2018/05/15																			
												chr		-		-																			
												appr		Nickor Zuo		2018/05/22		product family						ecn no		ELX-DG-30127-1									
										rel level						Released																			
surface 				linear		0.X		±0.30		Amphenol FCI						title		PCI EXPRESS 4.0						dwg no		10146027						rev		B	
						0.XX		±0.20																											
						0.XXX		±0.1																											
ASME Y14.5				angular		0°		±2°		www.fci.com						cat. no.		Product-Customer Drw						sheet 1 of 4											

A

B

C


D

A


B

C


D



SEE DETAIL A



DIM"G"
1.57 MM
2.0 MM
2.08 MM
2.31 MM
2.36 MM
2.40 MM



RECOMMENDED PCB LAYOUT

POSITION	N	DIM"F"
36	6	12.30
64	20	26.30
98	37	43.30
164	70	76.30


spec ref				dr		Jeny Ren	2017/11/01		projection 		MM 		size		A3		scale		2:1		
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED						eng					Jeny Ren		2018/05/15		ecn no ELX-DG-30127-1				
ASME Y14.5								chr					-		-						appr
surface 		linear		0.X		±0.30		Amphenol FCi		title PCI EXPRESS 4.0 STRADDLE MOUNT		dwg no 10146027		rev B							
				0.XX		±0.20															
				0.XXX		±0.1															
ASME Y14.5		angular		0°		±2°		www.fci.com		cat. no.		Product-Customer Drw				sheet 2 of 4					

A

B


C

D



I/O PANEL DIRECTION
PRIMARY (COMPONENT) SIDE

- NOTES:
1. NO TIE BAR PERMITTED FROM CARD EDGE TO LEADING EDGE OF PAD FOR PINS AI AND PIN "I".
 2. CHAMFER EDGES MUST BE FREE OF CUTTING BURRS.
 3. TOLERANCE : ± 0.13



POSITION	N	DIM"H"	PIN "I" (SEE NOTE 1)
36	6	8.15	B17
64	20	22.15	B31
98	37	39.15	B48
164	70	72.15	B81

spec ref	dr	Jeny Ren	2017/11/01	projection	MM	size	A3	scale	2:1
tolerance std	eng	Jeny Ren	2018/05/15	chr	-	ecn no	ELX-DG-30127-1	rel level	Released
ASME Y14.5	app	Nickor Zuo	2018/05/22	product family	PCI EXPRESS 4.0	rel level	Released	cat. no.	Product-Customer Drw
surface	linear	0.X	±0.30	Amphenol FCI	STRADDLE MOUNT	dwg no	10146027	rev	B
ASME Y14.5	angular	0°	±2°	www.fci.com		sheet 3 of 4			

NOTES:

- MATERIAL:
HOUSING: HIGH PERFORMANCE RESINS,BLACK,UL94 V-0 RATED.
CAP:HIGH PERFORMANCE RESINS,BLACK.
CONTACT: COPPER ALLOY.
- PLATING:
UNDERPLATE: 50 u" MIN NICKEL OVER ALL
SOLDER AREA: 100 u" MIN TIN(LEAD FREE)
MATING AREA: SEE PRODUCT PART NUMBER.
- PRODUCT SPECIFICATION: GS-12-1193
- PACKAGE SPECIFICATION: GS-14-2401.
- PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- ONLY P/N 10146027-XXXX10XX CAN GO IR REFLOW PROCESS.
- THIS PRODUCT WILL WITHSTAND EXPOSURE TO 260°C PACK TEMPERATURE
FOR 10 SECONDS IN REFLOW SOLDERING APPLICATION.
- DATE CODE BE PRINTED ON PROPER SURFACE.

PRODUCT PART NUMBER:

10146027- X X X X X X X X

NO. OF POSITION
36:36 POSITIONS
64:64 POSITIONS
98:98 POSITIONS
A4:164 POSITIONS


PCB THICKNESS OPTION
0:1.57 MM
1:2.0/2.08 MM
2:2.31/2.36/2.4 MM

LEAD FREE OPTION
LF:LEAD FREE

RESERVE
0

CAP OPTION (SEE NOTE 6)
0:WITHOUT CAP
1:CAP


CONTACT PLATING
0:15 u" Au
1:30 u" Au
2:15 u" GXT



DATA CODE INFORMATION

P X X X X X X X X X

PRODUCTION LINE CODE
DATE CODE THROUGH 01 TO 31
WEEK NUMBER 01 THROUGH 53
YEAR CODE; MOST RIGHT OF DIGIT
OF PRODUCTION.(e.g 2007=7)
MANUFACTURE SITE; 2 FOR DONGGUAN
SOURCE,P FOR CHINA

spec ref				dr		Jeny Ren	2017/11/01		projection		MM		size		A3		scale		2:1												
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng		Jeny Ren	2018/05/15						ecn no		ELX-DG-30127-1														
ASME Y14.5						chr		-		-							rel level				Released										
						appr		Nickor Zuo		2018/05/22											product family										
surface				linear		0.X		±0.30		Amphenol FCI		title		PCI EXPRESS 4.0						dwg no		10146027		rev		B					
																												0.XX		±0.20	
																												0.XXX		±0.1	
		ASME Y14.5		angular		0°		±2°		www.fci.com		cat. no.		Product-Customer Drw						sheet 4 of 4											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10146027-980000LF](#) [10146027-981010LF](#) [10146027-640000LF](#) [10146027-A420100LF](#) [10146027-A40000LF](#)
[10146027-982010LF](#)