


PHYSICAL

Conductors: 26 AWG 7/34 Tinned Copper  
Insulation: .010" Nom. PVC  
Color Code: Red, White, Black  
Temp. Rating: 80°C

ELECTRICAL

Voltage Rating: 300 V  
Current Rating: 1.6 A @ 10°C Rise Above Ambient  
Insulation Res.: 10<sup>10</sup> ohms – 10 ft Min.  
Cable Style: UL AWM Style 2697 (80°C, 300V)



DRAWN	PROD ENG	QA	MKT	P/ECN#	DRAWING NO. 111-2699-988	<b>AMPHENOL SPECTRA-STRIP</b> 720 SHERMAN AVE TEL (203) 281-3200 HAMDEN CT 06514 FAX (203) 281-5872	Rev -
5/15/98					TITLE: Spectra-Bond® Parallel Conductor Cable		SHEET 1 of 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[111-2699-988](#)