

RECOMMENDED
CABLE STRIPPING DIM'S

11.50 [.453]

28.60 [1.135]



3.90 [.154]

5.60 [.221]

4.00 [.158]

3.70 [.146]

8.30 [.327]



1. CRIMPED FERRULE
HEX CRIMP SIZE .213"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

<div><div>Amphenol Connex</div><div><div><div><div><div>Part Description</div><div>BNC CRIMP JACK (FOR RG-59/U CABLE) 50ohms</div></div><div><div>Part No.</div><div>112146</div></div></div><div><div>DWG. NO.</div><div>112146.DWG</div><div>REV. NC</div><div>SIZE A</div><div>SCALE NA</div></div></div></div></div>										<div>APPROVALS</div> <div>DATE</div>		<div><div><div><div>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR DISTANCE BETWEEN DRILL HOLES AND FOR DISTANCE BETWEEN PINS.</div><div>UNLESS OTHERWISE SPECIFIED, TOLERANCES ARE AS FOLLOWS: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED, DIMENSIONS FOR HOLE AND TAP ARE: 0.050 - .315 ± 0.007" .315 - 1.180 ± 0.015" 1.180 - 4.724 ± 0.020"</div></div></div></div>					DO NOT SCALE DRAWING	QTY	FINISH	MATERIAL	DESCRIPTION
DRAWN G.R.S.		05/12/05	CHECKED	ISSUED	SHEET 1 OF 1																
C:/112/112146.DWG																					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112146](#)