



REV.	DATE	DESCRIPTION
NC	04/18/05	INITIAL RELEASE



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .324"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

Amphenol Connex											
PART DESCRIPTION				BNC PANEL CRIMP JACK (RG-6/U CABLE)							
PART NO.				112727							
DWG. NO.				112727.DWG				REV. NC		SIZE A	
SCALE				NA							
APPROVALS		DATE									
DRAWN C.R.S.		04/18/05									
CHECKED											
SEALD											
BUILT 1 OF 1											
CADD FILE C:/112/112727.DWG											
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN [] ARE IN INCHES AND PER PART/UNIT REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR MILLIMETERS ARE: 0.5 - 0.9mm ± 0.20mm 1.0 - 3.0mm ± 0.40mm 3.0 - 12.0mm ± 0.50mm UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR INCHES ARE: .020 - .315 ± 0.007" .315 - 1.180 ± 0.015" 1.180 - 4.724 ± 0.020"											
DESCRIPTION		MATERIAL		FINISH		QTY		DO NOT SCALE DRAWING			
B											
7											
6											
5											
4		FERRULE		COPPER		NICKEL		1			
3		CONTACT PIN		PHOS. BRONZE		GOLD		1			
2		INSULATOR		TEFLON		NATURAL		1			
1		BODY		BRASS		NICKEL		1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112727](#)