




REV.	DATE	DESCRIPTION
NC	03/05/98	INITIAL RELEASE
A	03/11/07	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex							
7						DRAWN	G.R.S.	03/11/07									
6						CHECKED											
5						ISSUED			PART DESCRIPTION								
4									BNC P.C. MOUNT RECEPTACLE JACK								
3	CONTACT PIN	BER. COPPER	GOLD	1	DO NOT SCALE DRAWING	SHEET		1 OF 1		PART NO.							
2	INSULATOR	TEFLON	NATURAL	1		CAD FILE					112586						
1	BODY	DIECAST	NICKEL	1		C:/112/112586.DWG		DWG. NO.		112586.DWG		REV.	A	SIZE	A	SCALE	NA
	DESCRIPTION	MATERIAL	FINISH	QTY													

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112586-10](#)