





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-0C0672~675	2010/11/26	Ivan	Change View
C	LEN15C0443~449	2015/12/14	Ruru	Change Logo



BU-12BFFM-LL7000
Color: Black




BU-12BFFM-LL7A XX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
:
:
99 : 99Meters

Cable Length(L): 01~99Meters

- Note:
- * (XX) Important Dimension To Check.
 - * Waterproof Rate: IP67.
 - * Housing: Nylon+GF, Black
 - * Female Pin: Copper Alloy, Gold Plated
 - * O-Ring: EPDM, Black
 - * Lock Nut: Nylon+GF, Black
 - * Cable: UL2464 26AWG*12C+Drain+Al/My PVC Jacket UV Resistant, OD=6.0, Black.
 - * Cable Length Tolerance:
 - 01M~05M: ±60mm
 - 06M~10M: ±100mm
 - 11M~30M: ±200mm
 - 31M~99M: ±500mm



Pin Assignments
Front View 前視圖

12	Light Green	淺綠
11	Purple	紫
10	Orange	橙
9	Black	黑
8	Red	紅
7	Pink	粉紅
6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn	Wire Color	
Pin Out		

UNIT:mm		TOLERANCE		TITLE	
±0.5mm		Standard		Cable Lock 12Pin F Conn F Pin	
SCALE	1:1	SIZE	A4	SHEET	1 OF 1
REV.	C	WC-REV.	A.1	QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DWG NO	CUSTOMER	DRAWN BY	CHECKED BY	APPROVED BY	DATE
	BU-12BFFM-LL7AXX	ALTW	Ruru	Rita	Lisa	2015-12-14
						2015-12-14
						2015-12-14

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BU-12BFFM-LL7A02](#) [BU-12BFFM-LL7A01](#) [BU-12BFFM-LL7A05](#) [BU-12BFFM-LL7A10](#) [BU-12BFFM-LL7A03](#) [BU-12BFFM-LL7A08](#) [BU-12BFFM-LL7A15](#) [BU-12BFFM-LL7A04](#)