



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1610459~462	2016/01/18	Ruru	Change Logo & Note


F
E
D
C
B
A

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



Conn.

CDU-14BFMM-SL6000 ①
Color: Black



CDU-14BFMM-SL6AXX


XX:01~99Meters
01:01Meter
02:02Meters
⋮
99:99Meters

Cable Length(L):01~99Meters



Note:

- * @@Important Dimension.
- * Waterproof Rate: IP66
- * Housing: Nylon+GF,Black
- * Pin: Copper Alloy, Gold Plated
- * O-Ring: EPDM, Black
- * Nut: Nylon+GF, Black
- * Cable: UL2464 24AWG*14C+Drain+AL/My PVC Jacket, UV Resistant, OD=7.0mm, Black
- * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm



Pin Assignments
Front View

Brown/White	14
Black/White	13
Light Green	12
Pink	11
White	10
Gray	9
Purple	8
Blue	7
Green	6
Yellow	5
Orange	4
Red	3
Brown	2
Black	1
Wire Color	Conn.
Pin Out	

UNIT:mm		TITLE
TOLERANCE		Middle
±0.5mm		Cable Screw 14Pin F Conn M Pin
	SCALE	SHEET
	Free	1 OF 1
	REV.	SIZE
	B	A4
		QC :Inspection Item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Ruru	2016/01/18
DWG NO	CHECKED BY	DATE
CDU-14BFMM-SL6AXX	Rita	2016/01/18
CUSTOMER	APPROVED BY	DATE
ALTW	Lisa	2016/01/18

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CDU-14BFMM-SL6A05](#) [CDU-14BFMM-SL6A02](#) [CDU-14BFMM-SL6A10](#) [CDU-14BFMM-SL6A01](#) [CDU-14BFMM-SL6A03](#) [CDU-14BFMM-SL6A04](#)