

G Series

Black or chrome 3-1/4" diameter magnetic mount; 1-1/8"-18 thread

STANDARD CONFIGURATION

Model	Length of Coax	Coax	Connector*	Type
(R)(B)G-NC	12'	RG-58A/U	None	N/A
(R)(B)GC-NC	12'	RG-58/U	None	N/A
(R)(B)G	12'	RG-58A/U	PL259**	Crimp
(R)GP	12'	RG-58/U	PTFE PL259	Solder
(R)(B)GPL	12'	RG-58/U	Mini-UHF	Crimp
(R)GML195NCP	12'	Pro-Flex™ Plus 195	N	Crimp
(R)(B)GNCP	12'	RG-58/U	N	Crimp

For other cable types, lengths or connector configuration options, contact PCTEL Customer Service.



G

GM Series

Black or chrome 2-3/8" diameter magnetic mount; 1-1/8"-18 thread

STANDARD CONFIGURATION

Model	Length of Coax	Coax	Connector*	Type
(B)GM-NC	12'	RG-58A/U	None	N/A
(B)GMML195-NC	12'	Pro-Flex™ Plus 195	None	N/A
(B)GM	12'	RG-58A/U	PL259*	Crimp
(B)GMBN	12'	RG-58/U	BNC	Crimp
(B)GMC	12'	RG-58/U	TNC	Crimp
(B)GMML195C	12'	Pro-Flex™ Plus 195	TNC	Crimp
BGMFFME	12'	RG-58/U	Female FME**	Crimp
(B)GMSMA	12'	RG-58/U	Male SMA	Crimp
(B)GMPL	12'	RG-58/U	Mini-UHF	Crimp

For other cable types, lengths or connector configuration options, contact PCTEL Customer Service.



BGM



GM

G-AS Series

Black or Chrome All Surface Tape Mount; 3-1/4" diameter; 1-1/8"-18 thread

STANDARD CONFIGURATION

Model	Length of Coax	Coax	Connector*	Type
G-AS-NC	12'	RF-58A/U	None	N/A



G-AS-NC

* Connectors are shipped loose. Connectors may be attached upon request for an additional charge.** Connectors are attached on these models only.(R) prefix indicates an optional rubber boot(B) prefix indicates black optionFor other connector options, please refer to the Mobile Antenna Mounts Configurator Part Number Guide.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RG](#) [BGMML195NCP](#) [RBGNCP](#)