

		2	3	4	5	6	7	8																					
						<table><tr><th>REV.</th><th>ECN NO.</th><th>DATE</th><th>SIGN</th><th>DESCRIPTION</th></tr><tr><td>F</td><td>C221879</td><td>2022/12/20</td><td>Ruru</td><td> X1</td></tr><tr><td>G</td><td>C231032</td><td>2023/08/07</td><td>Ruru</td><td> X1</td></tr><tr><td>H</td><td>C240699</td><td>2024/06/20</td><td>Vicky</td><td> X2</td></tr></table>		REV.	ECN NO.	DATE	SIGN	DESCRIPTION	F	C221879	2022/12/20	Ruru	X1	G	C231032	2023/08/07	Ruru	X1	H	C240699	2024/06/20	Vicky	X2		
REV.	ECN NO.	DATE	SIGN	DESCRIPTION																									
F	C221879	2022/12/20	Ruru	X1																									
G	C231032	2023/08/07	Ruru	X1																									
H	C240699	2024/06/20	Vicky	X2																									
Recommended Panel Cut-Out																													
				Wire harness		Connector																							
				Shield		Nut																							
				O-Ring		M16*1.5																							
		 MI2D-XXPFFC-SF8CXX																											
		XX: No. Of Pin		 15:150mm 20:200mm 95:950mm Cable Pitch Unit:50mm A0:1000mm A5:1500mm Cable Pitch Unit:100mm Wire Length(L):150~1500mm																									
						Note: * RoHS Compliant * Important dimension Waterproof rate: IP68, unmated 1m/24h IP69K, mated * Connector Housing: Thermoplastic, Black Pin: Copper alloy, Gold plated O-Ring: Rubber, Green * Shield: Metal * Nut: Metal * O-Ring: Rubber, Black * Wire harness: UL1061, 22AWG * For panel thickness max: 4.5mm * O-Ring and nut are assembled on connectors * Wire harness tolerance: 150mm < L ≤ 300mm: ±15mm 300mm < L ≤ 1000mm: ±20mm 1000mm < L ≤ 1500mm: +50/-0mm																							
								</																					

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[M12D-04PFFC-SF8C30](#) [M12D-04PFFC-SF8C15](#) [M12D-04PFFC-SF8C50](#) [M12D-04PFFC-SF8CA0](#) [M12D-04PFFC-SF8C20](#)