




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-7B0141	2007/11/15	Gao Ling	Modify Panel Thickness
C	LEN1640314	2016/04/18	Vicky	Update Logo
D	C240125	2024/01/24	Vicky	 X2



Recommended Panel Cut-Out




DETAIL A
SCALE 2:1






Pin Assignments




Front View



PCB Layout



 Note:

- *  Important dimension
- * Waterproof Rate: IP68, unmated 1m/24h
- * Connector
 - Housing: Thermoplastic, Black
 - USB B: Female PCB Type, Gold Plated
- * Nut: Thermoplastic, Black
- * Gasket: Rubber, Black
- *  Use with waterproof cap or dust cap
For Panel Thickness Max: 2.8mm
- *  Use without waterproof cap or dust cap
For Panel Thickness Max: 4.0mm
- * Gasket and nut are packed separately in pe bag

UNIT:mm			TITLE USB, B TYPE, 2.0, FRONT FASTENED M, F, PCB S, SCREW				<h1>Amphenol LTW</h1> <h2>安費諾亮泰企業股份有限公司</h2>		ITEM NO UB-20PMFP-SC800I	DRAWN BY Vicky	DATE 2024-01-24
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±		SCALE 3:2		SIZE A4	SHEET 1 OF 1				DWG NO UB-20PMFP-SC800I	CHECKED BY Rita	DATE 2024-01-24
		REV. D		WC-REV. A.4	QC: Inspection item				CUSTOMER ALTW	APPROVED BY Fred	DATE 2024-01-24

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[UB-20PMFP-SC8001](#)