


Symbol	Count	Description	Drawn	Approved	Date
	4	a. Contact 역삼방지 수경 b. 도금 Pd-Ni계 반광, 단자의 접촉부 R* 추가	JonuLim		12.05.31
	2	a. Bracket 삼방 부를 도금: 1.2-->50.95 b. 세출 반광: PA46-->PA6T	JonuLim		12.07.18

— NOTE —



- ☆ mark are CTQ dimensions.
- Otherwise tolerance: ±0.05
- Coplanarity: Max. 0.08

CTQ Dimension	
☆(1)	9.70 ⁺⁰ _{-0.1}
☆(2)	1.50±0.05
☆(3)	10.20±0.05
☆(4)	0.08 Max.



No	Part name	Q'ty	Material	Finish	Remark
3	Bracket	4	SUS-301		
2	CONTACT	5	C7025-TMO2	Ni 2-5um + Pd-Ni 0.75um min. + Au 0.05um min.	
1	HOUSING	1	PA6T (HTN)		

Drawn by	Model name	SP Battery connector	Model No.	202-02970-00518
Designed by	Part name	Male assembly	Part No.	
Checked by	Date	Mr.22.2009	3rd ANGLE	
Scale	N/S	Unit	mm	
Approved by	Shale	Task	Y	Part reference
Shale		Reference	Con	stuent
		Other		



Otherwise Tolerance	
X	±0.1
X.XX	±0.05
X.XXX	±0.02
Angle : ±1°	
Chamfer or Round	: 0.05 Max

Amphenol CIK

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[202-02970-00518](#)