


REV.	DATE	ECR NO.	DESCRIPTION
NC	04/10/07	-	INITIAL RELEASE
A	08/19/08	100047	ADD "50 ohms" TO PART DESCRIPTION



8				<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.</small> <small>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:</small> 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm <small>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:</small> .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	<h1 style="color: blue;">Amphenol Connex</h1>				
7					DRAWN	GRS					08/19/08
6					CHECKED			PART DESCRIPTION BNC JACK TO SMB PLUG ADAPTER - 50 ohms			
5					ISSUED						
4	CONTACT PIN	BER. COPPER	GOLD		1	SHEET	1 OF 1	PART NO. 242185			
3	INSULATOR	PTFE	NATURAL	1	CAD FILE	C:/242/242185.DWG	DWG. NO.				
2	SMB BODY	BRASS	GOLD	1							
1	BNC BODY	BRASS	NICKEL	1							
	DESCRIPTION	MATERIAL	FINISH	QTY							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[242185](#)