





PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
C	DCN 42164	03/16	DAL
D	DCN 48135	11/18	STW



MATERIAL:

BODY, CONTACT & RETAINING RING:	BERYLLIUM COPPER
INSULATOR:	PTFE
FERRULE:	BRASS
COMPRESSION SPRING, SLEEVE & WASHER:	STAINLESS STEEL


FINISH:

BODY, CONTACT & FERRULE:	GOLD OVER NICKEL
RETAINING RING:	NICKEL
COMPRESSION SPRING, SLEEVE & WASHER:	PASSIVATED

PERFORMANCE:

IMPEDANCE:	50 OHMS
FREQ. RANGE:	DC TO 40.0 GHz.
VSWR:	1.30:1 DC TO 40.0 GHz.

RECOMMENDED MOUNTING HOLE

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15' DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005 INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS	 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409			
FINISH:	SEE NOTES			TITLE: VITA 67.1/2 PLUG-IN CONTACT FOR Ø.085 CABLE			
SURFACE AREA:	N/A						
PROPRIETARY		THIRD ANGLE PROJECTION 		DRAWN:	JMC 12/20/10		
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.				CHECKED:	STW 12/20/10		
				APPROVED:	STW 12/20/10		
			SIZE	CAGE CODE	DWG. NO.		
			B	95077	3221-40022		
			SCALE: 10:1		SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[3221-40022](#)