




DimA=N×5.08
DimB=(N-1)×5.08
N=NUMBER OF CONTACTS

POLES	TOL
2p-6p	+0.10/-0.10
7p-12p	+0.20/-0.20
13p-18p	+0.30/-0.30
19p-24p	+0.40/-0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	08/04'06	Current rating is changed from 10A to 20A	Marvin
△	08/04'06	Solid wire(AWG) standard is changed from 12-30 to 12-22	Marvin
△	08/04'06	Stranded wire(AWG) standard is changed from 12-30 to 12-22	Marvin
△	08/04'06	Torque standard is changed from 5 Lb-In to 4 Lb-In	Marvin
△	6/03'08	Operating temperature is changed	Marvin
△	6/03'08	Dimension is changed from 2.54 to 2.64	Marvin
△	2010.04.01	Add the 2p mark	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item ③ Clamp: Brass(CuZn) Ni plated
- Item ① Terminal screw: Steel Zinc plating "-" slot type
- Item ③ Female contact: PhBz ,Tin plated
- Item ④ Terminal (up body): Thermoplastic (UL94V-0)
- Item ⑤ Terminal (down body): Thermoplastic (UL94V-0)
- Item ① Flange screw: Steel Zinc plating "+/-" slot type
- Electrical cULus
- Voltage rating: 300VAC
- △ ● Current rating: 20A
- Wire range:
- △ ● Solid wire(AWG): 12-22
- △ ● Stranded wire(AWG): 12-22
- △ ● Torque: 4 Lb-In
- Screw: M3
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- △ ● Operating temperature: -40°C to +115°C
- Safety Approval: 

EM xx 51 x 2 xxxx G

02 2 CONTACTS	Color	0000: "@" Logo	RoHS
03 3 CONTACTS	0 Black (RAL9005)	000A: "ANYTEK" Mark	Pb<40,000ppm
...	2 Red (RAL3001/D)	Any special item by	
24 24 CONTACTS	3 Orange(RAL2011/P)	customer request.	
	4 Yellow(RAL1018/A)	please contact sales	
	5 Green(RAL6018/T)	department.	
	6 Blue (RAL5015/A)		
	8 Grey(RAL7035/D)		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		EM-5.08 Series with flange						
PART NO.		EMxx51x2xxxxG			DWG NO.	8EM0002		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Jacke 2010.04.01	Jacke 2010.04.01		UNIT: mm		X.	±0.50
					SCALE: NONE		X.X	±0.30
					SHEET: 01/01		X.XX	±0.10
					REV.: E		X°	±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>EM0251520000G</u>	<u>EM0351520000G</u>	<u>EM0451520000G</u>	<u>EM0551520000G</u>	<u>EM0651520000G</u>	<u>EM0751520000G</u>
<u>EM0851520000G</u>	<u>EM0951520000G</u>	<u>EM1051520000G</u>	<u>EM1151520000G</u>	<u>EM1251520000G</u>	<u>EM1351520000G</u>
<u>EM1451520000G</u>	<u>EM1551520000G</u>	<u>EM1651520000G</u>	<u>EM1751520000G</u>	<u>EM1851520000G</u>	<u>EM1951520000G</u>
<u>EM2051520000G</u>	<u>EM2151520000G</u>	<u>EM2251520000G</u>	<u>EM2351520000G</u>	<u>EM2451520000G</u>	<u>EM1051020000G</u>
<u>EM0851020000G</u>	<u>EM02018000J0G</u>				