





PRODUCT NO.


SEE TABLE



mat'l. code				surface	tolerance	projection	product family
ISO1302				ISO1101	ISO406		MOD JACK
tolerances unless otherwise specified				mm			
R S00022 BC L 01/26/00				0.X±0.3			
S N05-0002 YS 01/07/05				0.XX±0.15			
T N06-0130 LONG 5/15/06				0.XXX±0.05			
U N08-0097 SH MMD 5/10/08				dr JANET	01/26/00		
V ELX-N-010699 SH MMD 03/14/12				engr TONY CHIEN	01/26/00		
				chr TONY CHIEN	01/26/00		
				appd JENN TSAO	01/26/00		
sheet index	revision	nv	v				
sheet	1	2					

product family	MOD JACK
title	6 POS HORIZONTAL P.C.B. MOD JACK ASSY
dwg no	68898
sheet 1 of 2	A4
type	Product Customer Drawing


PRODUCT NO. (NOTE 1)	POSITIONS LOADED	CONTACT PLATING	HOUSING COLOR	EARS	REMARKS
68898-001/-001LF	ALL	5u" Au + high performance lubricant @ TM	BLACK	YES	-
68898-001R/-001RLF	ALL	5u" Au + high performance lubricant @ TM	RED	YES	-
68898-001G/-001GLF	ALL	5u" Au + high performance lubricant @ TM	GREEN	YES	-
-002/-002LF	2,3,4,5	5u" Au + high performance lubricant @ TM	BLACK	YES	-
-003/-003LF	3,4	5u" Au + high performance lubricant	BLACK	YES	-
-004/-004LF	2,3,4,5	5u" Au + high performance lubricant	BLACK	YES	-
-005/-005LF	ALL	5u" Au + high performance lubricant	BLACK	YES	-
-006/-006LF	3,4	5u" Au + high performance lubricant @ TM	BLACK	YES	-
-007	2,3,4,5	GXT @ TM	GRAY	YES	OBSOLETE
-008/-008LF	ALL	5u" Au + high performance lubricant	BLACK	NO	-
-009/-009LF	2,3,4,5	1,27um /50u" GXT	BLACK	YES	-
-010/-010LF	ALL	1,27um /50u" GXT	BLACK	YES	-
-011/-011LF	2,3,4,5	2u" GXT	BLACK	YES	-
-012/-012LF	2,3,4,5	6u" GXT	BLACK	YES	-
-013/-013LF	ALL	5u" Au + high performance lubricant @ TM	BLACK	YES	HI TEMP MATERIAL
-014/-014LF	3,4	6u" GXT	BLACK	YES	-
-015/-015LF	3,4	5u" Au + high performance lubricant @ TM	BLACK	NO	-
-016/-016LF	2,3,4,5	5u" Au + high performance lubricant @ TM	BLACK	NO	-
-017LF	ALL	5u" Au + high performance lubricant @ TM	BLACK	YES	-



VIEW A-A

NOTES :

- WHEN PRODUCT CALLS FOR PACKAGING IN TRAY ORDER THE PRODUCT WITH PART NUMBER 68898-XXXT OR -XXXTLF FOR PACKAGING IDENTIFICATION. FOR PRODUCT NUMBER WITHOUT SUFFIX "T" OR "TLF", THE PRODUCT WILL BE PACKED IN TUBE AS PER DUPONT STANDARD PACKAGING.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- IF LF P/N PACKAGING MEETS GS-14-920 SPECIFICATION.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.60mm MINIMUM THICK CIRCUIT BOARD.
- FOR 68898-013/013LF THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- EQUIVALENT THICKNESS Au AND GXT PLATING HAVE SAME FUNCTION AND THEY ARE ALTERNATIVE BY THE CUSTOMER.



mat'l. code				surface	tolerance	projection	product family
ISO1302				ISO1101	ISO406		MOD JACK
l	tr	ec	n	no	dr	date	tolerances unless otherwise specified
R	S00022	BC	L	01/26/00	angle	0.1X±0.3	mm
S	N05-0002	YS	01/07/05	0.1X±0.15	scale	2.0	
T	N06-0130	LONG	5/15/06	0.1X±0.05			
U	N08-0097	SH	MMQ	5/10/08	dr	JANET	01/26/00
V	ELX-N-010699	SH	MMQ	03/14/12	engr	TONY CHIEN	01/26/00
					chr	TONY CHIEN	01/26/00
					appd	JENN TSAO	01/26/00
sheet	revision						
index	sheet						



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[68898-002](#) [68898-006](#) [68898-009](#) [68898-010](#) [68898-008](#) [68898-001LF](#) [68898-002LF](#) [68898-005LF](#) [68898-009LF](#)
[68898-010LF](#) [68898-001](#)