

ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	NRN 44554	01/20	MKK

MATERIAL:

CONNECTORS:

CABLE:

SHRINK TUBING:

2X SMA MALE R/A (SF2912-60955)

FLEXIBLE Ø.047 CABLE

M23053/5

PERFORMANCE:



IMPEDANCE:

FREQ. RANGE:

50 OHMS

DC TO 18.0 GHz

SV P/N	OAL
7029-3379	6.000
7029-3380	12.000

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS	<div> www.svmicrowave.com</div> <div>TITLE: SMA R/A MALE TO SMA R/A MALE Ø.047 CABLE ASSEMBLY</div>	
FINISH:	SEE NOTES	FRACTIONAL: ±1/64    ANGULAR: X° ±1°0'    X°X' ±15'			
SURFACE AREA:	N/A	DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005			
PROPRIETARY THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.					
THIRD ANGLE PROJECTION			DRAWN: SJ 01/22/20	SIZE DWG. NO.	
<div></div>			CHECKED: MKK 1/30/20	<div>B</div> 7029-3379-3380	
			APPROVED: MKK 1/30/20	SCALE: 4:1	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7029-3379](#) [7029-3380](#)