

ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	NRN 40686	06/16	STW

MATERIAL:

SMPM FEMALE R/A CONNECTOR: 3222-40006

2.92MM MALE CONNECTOR: SF1511-60069

STANDARD FLEXTRA CABLE: 200-70-214

SINGLE WALL TUBING: M23053/5 (BLACK)

PERFORMANCE:


IMPEDANCE: 50 OHMS

FREQ. RANGE: DC TO 32 GHz

VSWR: 1.61:1, DC TO 32 GHz

INSERTION LOSS: SEE TABLE

TABLE I		
SV P/N	L (IN)	INSERTION LOSS dB MAX.
7032-6759	6.00	1.77
7032-6760	12.00	2.99

MATERIAL: SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15' DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005 INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63+MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS	 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409	
FINISH: SEE NOTES				TITLE: SMPM FEMALE R/A TO 2.92MM MALE Ø.047 CABLE ASSEMBLY
SURFACE AREA: N/A				SIZE CAGE CODE DWG. NO. B 95077 7032-6759-6860
PROPRIETARY THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.	THIRD ANGLE PROJECTION 	DRAWN: MAL 06/16/16 CHECKED: STW 06/16/16 APPROVED: STW 06/16/16	SCALE: 3:1 SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7032-6759](#)