

SECTION A-A

Poles	01	02	03	04	05	06	07	08
Dim L	7.85	14.2	20.55	26.9	33.25	39.6	45.95	52.3
Dim B		6.35	12.70	19.05	25.40	31.75	38.10	44.45
TOL	±0.10		±0.15		±0.20		±0.25	
Poles	09	10	11	12	13	14	15	16
Dim L	58.65	65.0	71.35	77.7	84.05	90.4	96.75	103.1
Dim B	50.80	57.15	63.50	69.85	76.20	82.55	88.90	95.25
TOL	±0.30		±0.35		±0.40			

SIGN	DATE	DESCRIPTION	APPROVER
△	2010.05.31	Add cULus standard	Jacke
△	06/21`11	The dimension is changed from 10.16 to 10.16±0.15	Tason
△	06/21`11	Critical dimension is changed.	Tason
△	06/21`11	The tolerance table is changed.	Tason
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item a Terminal body;Thermoplastic (UL94V-0)
- Item b Terminal cover;Thermoplastic (UL94V-0)
- Item c Terminal screw ;Steel Zinc plating "-" slot type
- Item d Clampage;Steel/steel Zinc plated
- Item e Terminal body;Steel, Zinc plating
- Item f Solder pin;Copper, Tin plated

Electrical

- Voltage rating: 300VAC
- Current rating: 30A
- Wire range:
- Solid wire(AWG): 10-24
- Stranded wire(AWG): 10-24
- Torque(Lb-In): 4.3
- Screw: M3
- Wire strip length: 15-16mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec

△ Critical dimension: ▽

△ Safety Approval: cULus


KH xx 05 x 0 xxxx G

01 1 CONTACTS	0 Black (RAL9005)	0000 Standard @ Logo	RoHS
02 2 CONTACTS	2 Red (RAL3001/D)	000A Standard ANY Logo	Pb<40,000ppm
03 3 CONTACTS	3 Orange(RAL2011/P)	Any special item by customer request, please contact sales department.	
04 4 CONTACTS	4 Yellow(RAL1018/A)		
05 5 CONTACTS	5 Green(RAL6018/T)		
06 6 CONTACTS	6 Blue (RAL5015/A)		
07 7 CONTACTS	7 Grey(RAL7035/D)		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KH 6.35 Series 90DWire inlet								
PART NO.	KHxx05x0xxxxG			DWG NO.	8KH0002				
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
		Tason 2011.06.21	Jacke 2009.05.18					UNIT: mm	X.
					SCALE: NONE		X.X	±0.30	
				SHEET: 01/01	REV.: B		X.XX	±0.10	
							X°	±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[KH0205500000G](#) [KH0305500000G](#) [KH0405500000G](#) [KH0505500000G](#) [KH0605500000G](#) [KH0705500000G](#)
[KH0805500000G](#) [KH0905500000G](#) [KH1005500000G](#) [KH1105500000G](#) [KH1205500000G](#) [KH1305500000G](#)
[KH1405500000G](#) [KH1505500000G](#) [KH1605500000G](#)