



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-710100~103	2007/01/12	R.Bondoc	Change Nut BAB0040NI00 To BEA00010016.
C	LEN-920185~188	2009/02/04	Vicky	Update the drawing.
D	LEN1630093~096	2016/02/18	Ruru	Change Logo

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.




Cable ②

8-03AFFM-SL7000 ①
Color: Black



8-03AFFM-SL7AXX
XX:01~99Meters
01:01Meter
02:02Meters
:
:
99:99Meters
Cable Length(L):01~99Meters



Pin Assignments
Front View

4	Black	黑
3	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		

- Notes:
- * @ Important Dimension.
 - * Waterproof Rate:IP67.
 - * Connector:Black,PU.
 - * Female Pin:Copper Alloy,Gold Plated.
 - * Cable:UL2464 22AWG*3C+Talcum,Black, PVC Jacket,UV Resistant,OD=5.0mm.
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TITLE	M8 Conn	
TOLERANCE			Cable Screw 3P F Conn F Pin	
±0.5 mm		SCALE	Free	SHEET 1 OF 1
REV. D	SIZE A4	QC :Inspection Item		

Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO	DRAWN BY Ruru		DATE 2016/02/18
		DWG NO 8-03AFFM-SL7AXX	CHECKED BY Rita		DATE 2016/02/18
		CUSTOMER ALTW	APPROVED BY Lisa		DATE 2016/02/18

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8-03AFFM-SL7A05](#) [8-03AFFM-SL7A10](#) [8-03AFFM-SL7A01](#) [8-03AFFM-SL7A02](#)