


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-920030~033	2009/02/02	Vicky	Update the drawing.
C	LEN1510241~244	2015/01/06	Sam	Update logo.




8-03BMMM-SR7AXX

XX: 01~99Meters
01: 01Meter
02: 02Meters

99: 99Meters

Cable Length(L): 01~99Meters



Pin Assignments
Front View

4	Black	黑
3	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		

Notes:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP67.
- * Connector: PU, Black.
- * Male Pin: Copper Alloy, Gold Plated.
- * Cable: UL2464 22AWG*3C+Talcum, Black, PVC Jacket, UV Resistant, OD=5.0mm.
- * Cable Length Tolerance: 01M: ± 40 mm
02M~05M: ± 60 mm
06M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm

UNIT:mm	
TOLERANCE	± 0.5 mm

TITLE Δ M8 Conn Cable Screw 3P M Conn M Pin			
SCALE	3:2	SIZE	A4
REV.	C	WC-REV.	A.1
SHEET 1 OF 1			
QC: Inspection item			

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Sam	2015-01-06
CUSTOMER	CHECKED BY	DATE
ALTW	Vicky	2015-01-06
	APPROVED BY	DATE
	Rita	2015-01-06

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8-03BMMM-SR7A01](#) [8-03BMMM-SR7A05](#) [8-03BMMM-SR7A02](#) [8-03BMMM-SR7A10](#)