



Recommended
Panel Cut-Out



ENote:

- * **OC** Important Dimension.
- * Waterproof Rate: IP67
- * Housing: Black, Nylon+GF
- * Male Pin: Copper Alloy, Gold Plated
- * Shield: Zinc Alloy, Nickel Plated

C

- * Nut: Copper Alloy, Nickel Plated
- * O-Ring: Black, EPDM

B

- * Panel Thickness For Snap-in Type Max 3.0mm
- * Panel Thickness For Screw Type Max 1.9mm
- * Nut Torque: 4-6 kgf.cm

UNIT: mm				TITLE  M8 Conn Panel Screw 3P M Conn M Pin			Amphenol LTW 安費諾亮泰企業股份有限公司			ITEM NO 8-03PMMP-SF7001		DRAWN BY Galaxy		DATE 2013-01-29				
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°				SCALE 3:1		SIZE A4				SHEET 1 OF 1		DWG NO 8-03PMMP-SF7001		CHECKED BY Aric		DATE 2013-01-29		
				REV. E		WC-REV. B.2				QC: Inspection item		CUSTOMER ALTW		APPROVED BY Maslow		DATE 2013-01-29		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8-03PMMP-SF7001](#)