







REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-7A0180	2007/09/29	Myrdal	Added Note
C	LEN-910179	2009/01/07	Ivan Lin	Change rev. to ECN note
D	CI92160	2019-12-21	Peng	$\triangle$ XI




3 Pin Male Connector
Male Pin PCB Layout



Pin Assignments
Front View



Recommended
Panel Cut-Out



- $\triangle$ Note:
- * CC Important Dimension.
 - * Waterproof Rate: IP67
 - * Housing: Black, Nylon+GF
 - * Male Pin: Copper Alloy, Gold Plated
 - * Shield: Zinc Alloy, Nickel Plated
 - * $\triangle$ Nut: Copper Alloy, Nickel Plated
 - * O-Ring: Black, EPDM
 - * Panel Thickness For Snap-in Type Max 3.0mm
 - * $\triangle$ Panel Thickness For Screw Type Max 1.9mm
 - * Nut Torque: 4-6 kgf.cm

UNIT:mm	
TOLERANCE	
.X	± 0.25
.XX	± 0.1
.XXX	± 0.05
ANGLES	$\pm 1^\circ$

TITLE	$\triangle$ M8 Conn Panel Screw 3P M Conn M Pin		
SCALE	3:1	SIZE	A4
REV.	D	WC-REV.	A.3
CC : Inspection item			

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	8-03PMMP-SF7002	DRAWN BY	Ivan Lin	DATE	2009/01/07
DWG NO	8-03PMMP-SF7002	CHECKED BY	Tommy Hom	DATE	2009/01/07
CUSTOMER	ALTW	APPROVED BY	Luke Chang	DATE	2009/01/07

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8-03PMMP-SF7002](#)