



Notes:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP67.
- * Connector: PU, Black.
- * Female Pin: Copper Alloy, Gold Plated.
- * Cable: 22AWG*4C+Insulation, PU, OD=4.8mm, Black.
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



4	Black	黒
3	Blue	藍
2	White	白
1	Brown	棕
Conn.	Wire Color	
Pin Out		

UNIT:mm	
TOLERANCE	
± 0.5 mm	

 M8 Conn Cable Screw 4P F Conn F Pin		
SCALE	Free	SHEET 1 OF 1
REV.	D	SIZE A4
 : Inspection Item		

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Ruru	DATE 2016/02/01
DWG NO 8-04BFFM-SL7BXX	CHECKED BY Rita	DATE 2016/02/01
CUSTOMER AI TW	APPROVED BY Lisa	DATE 2016/02/01

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8-04BFFM-SL7B02](#) [8-04BFFM-SL7B10](#) [8-04BFFM-SL7B05](#) [8-04BFFM-SL7B01](#)