




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-920048~051	2009/02/03	Vicky	Update the drawing.
C	LEN1510250~253	2015/01/06	Sam	Update logo.



8-04BFFM-SR7AXX
XX: 01~99Meters
01: 01Meter
02: 02Meters
.....
99: 99Meters
Cable Length(L): 01~99Meters



Pin Assignments
Front View

4	Black	黑
3	Blue	藍
2	White	白
1	Brown	棕
Conn.	Wire Color	
Pin Out		

- Notes:
- * $\varnothing$ Important Dimension.
 - * Waterproof Rate: IP67.
 - * Connector: PU, Black.
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Cable: UL2464 22AWG*4C+Talcum, Black, PVC Jacket, UV Resistant, OD=5.0mm.
 - * Cable Length Tolerance: 01M: ± 40 mm
02M~05M: ± 60 mm
06M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm

UNIT: mm				TITLE Δ M8 Conn Cable Screw 4P F Conn F Pin		ITEM NO		DRAWN BY Sam		DATE 2015-01-06	
TOLERANCE		± 0.5 mm		SCALE 3:2		DWG NO 8-04BFFM-SR7AXX		CHECKED BY Vicky		DATE 2015-01-06	
REV. C		WC-REV. A.1		SHEET 1 OF 1		CUSTOMER ALTW		APPROVED BY Rita		DATE 2015-01-06	
				$\varnothing$ Inspection item							

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8-04BFFM-SR7A05](#) [8-04BFFM-SR7A02](#) [8-04BFFM-SR7A10](#) [8-04BFFM-SR7A01](#)