



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Conn.

Cable ② 8A-02AFFM-SL7000
Color: Black

8A-02AFFM-SL7AXX
XX: 01~99Meters
01: 01Meter
02: 02Meter
:
99: 99Meters
Cable Length(L): 01~99Meters



2	Red 紅
1	Black 黑
Conn.	Wire Color
Pin Out	

Note:
* CC Important Dimension.
* Waterproof Rate: IP67.
* Connector: PU, Black.
* Female Pin: Copper Alloy, Gold Plated.
* Screw Nut: Zinc Alloy, Nickel Plated.
* O-Ring: Viton, Green.
* Cable: UL2464 22AWG*2C+Talcum, PVC Jacket, UV Resistant, OD=4.2, Black.
* Cable Length Tolerance: 01M: $\pm 40\text{mm}$
02~05M: $\pm 60\text{mm}$
06~10M: $\pm 100\text{mm}$
11~30M: $\pm 200\text{mm}$
31~99M: $\pm 500\text{mm}$

UNIT:mm		TITLE M8 2Pin Cable F Conn. F Pin
TOLERANCE $\pm 0.5 \text{ mm}$	SCALE 2:1	SIZE A4
	REV. A	WC-REV. A.3
		CC : Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Mila	DATE 2014-01-09
DWG NO 8A-02AFFM-SL7AXX	CHECKED BY Jimmy	DATE 2014-01-09
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2014-01-09

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8A-02AFFM-SL7A02](#) [8A-02AFFM-SL7A01](#)