




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



8A-02AMMM-SL7AXX
XX: 01~99Meters
01: 01Meter
02: 02Meter
:
99: 99Meters
Cable Length(L): 01~99Meters

- Note:
- * (CC) Important Dimension.
 - * Waterproof Rate: IP67.
 - * Connector: PU, Black.
 - * Male Pin: Copper Alloy, Gold Plated.
 - * Screw Nut: Zinc Alloy, Nickel Plated.
 - * Cable: UL2464 22AWG*2C+Talcum, PVC Jacket, UV Resistant, OD=4.2, Black.
 - * Cable Length Tolerance: 01M: ±40mm
02~05M: ±60mm
06~10M: ±100mm
11~30M: ±200mm
31~99M: ±500mm



2	Red 紅
1	Black 黑
Conn.	Wire Color
Pin Out	

UNIT:mm		TITLE
TOLERANCE	±0.5 mm	M8 2Pin Cable M Conn. M Pin
SCALE	2:1	SIZE A4
REV.	A	WC-REV. A.6
SHEET 1 OF 1		
(CC): Inspection item		

ITEM NO		DRAWN BY	DATE
DWG NO		CHECKED BY	DATE
CUSTOMER		APPROVED BY	DATE
8A-02AMMM-SL7AXX		Mila	2014-01-09
ALTW		Jimmy	2014-01-09
		Jerry	2014-01-09

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8A-02AMMM-SL7A01](#)