









REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Pin Assignment
Front View



Recommended
Panel Cut-Out

Note:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP67.
- * Housing: Nylon+GF, Black.
- * Male Pin: Copper Alloy, Gold Plated.
- * Shield: Zinc Alloy, Nickel Plated.
- * Screw Nut: Copper Alloy, Nickel Plated.
- * O-Ring: EPDM, Black.
- * For Panel Thickness Max 3.5mm.
- * Nut Torque: 4~6 kgf.cm.

UNIT:mm				TITLE M8 4Pin Panel M Conn. M Pin			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO 8A-04PMMS-SH7001		DRAWN BY Tony_leng		DATE 2013-10-22	
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 3:1	SIZE A4	SHEET 1 OF 1				DWG NO 8A-04PMMS-SH7001		CHECKED BY Jimmy		DATE 2013-10-22		
REV. A		WC-REV. A.1	QC: Inspection item		CUSTOMER ALTW			APPROVED BY Jerry		DATE 2013-10-22				

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8A-04PMMS-SH7001](#)