




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.




REV.	ECN NO.	DATE	SIGN	DESCRIPTION



8AP-04AMMM-SL7AXX
XX: 01~99Meters
01: 01Meter
02: 02Meter
:
99: 99Meters
Cable Length(L): 01~99Meters

Note:
* (CC) Important Dimension.
* Waterproof Rate: IP67.
* Connector: PU, Black.
* Male Pin: Copper Alloy, Gold Plated.
* Screw Nut: Nylon+GF, Black.
* Cable: UL2464 22AWG*4C+Talcum, PVC Jacket, UV Resistant, OD=5.0, Black.
* Cable Length Tolerance: 01M: ±40mm
02~05M: ±60mm
06~10M: ±100mm
11~30M: ±200mm
31~99M: ±500mm



Pin Assignments
Front View

4	Black 黑
3	Blue 藍
2	White 白
1	Brown 棕
Conn.	Wire Color
Pin Out	

UNIT:mm		TITLE	M8 4Pin Cable M Conn. M Pin	
TOLERANCE		SCALE	2:1	SIZE A4
±0.5 mm		REV.	A	WC-REV. A.2
		(CC): Inspection item		

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DWG NO	CUSTOMER	DRAWN BY	CHECKED BY	APPROVED BY	DATE
	8AP-04AMMM-SL7AXX	ALTW	Mila	Jimmy	Jerry	2014-01-09
						2014-01-09
						2014-01-09

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8AP-04AMMM-SL7A01](#)