





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



8AP-06AFFM-QL5AXX
XX: 01~99Meters
01: 01Meter
02: 02Meter
:
99: 99Meters
Cable Length(L): 01~99Meters

Note:
* $\varnothing$ Important Dimension.
* Waterproof Rate: IP65.
* Connector: PU, Black.
* Female Pin: Copper Alloy, Gold Plated.
* Cable: UL2464 24AWG*6C+Al/Mylar, PVC Jacket, UV Resistant, OD=5.0, Black.
* Cable Length Tolerance: 01M: ± 40 mm
02~05M: ± 60 mm
06~10M: ± 100 mm
11~30M: ± 200 mm
31~99M: ± 500 mm



6	Green 綠
5	Yellow 黃
4	Orange 橘
3	Red 紅
2	Brown 棕
1	Black 黑
Conn.	Wire Color

UNIT:mm		TITLE
TOLERANCE	± 0.5 mm	M8 6Pin Cable F Conn. F Pin
SCALE	2:1	SIZE A4
REV.	A	WC-REV. A.1
		$\varnothing$: Inspection item

ITEM NO	DRAWN BY	DATE
DWG NO	Tony-leng	2013-10-24
CUSTOMER	CHECKED BY	DATE
ALTW	Jimmy	2013-10-24
	APPROVED BY	DATE
	Jerry	2013-10-24

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8AP-06AFFM-QL5A01](#)