


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Cable ②



8H-05AFFM-SR7000
Color: Black

①

8H-05AFFM-SR7AXX

XX: 01~99Meters
01: 01Meter
02: 02Meter
:
:
99: 99Meters

Cable Length(L): 01~99Meters



Pin Assignments
Front View

5	Yellow 黃
4	Orange 橘
3	Red 紅
2	Brown 棕
1	Black 黑
Conn.	Wire Color

Pin Out

Note:

- * ① Important Dimension.
- * Waterproof Rate: IP67.
- * Connector: PU, Black.
- * Female Pin: Copper Alloy, Gold Plated.
- * Screw Nut: Zinc Alloy, Nickel Plated.
- * O-Ring: Viton, Green.
- * Cable: UL2464 24AWG*5C+Talcum, PVC Jacket, UV Resistant, OD=5.0, Black.
- * Cable Length Tolerance: 01M: ±40mm
02~05M: ±60mm
06~10M: ±100mm
11~30M: ±200mm
31~99M: ±500mm

UNIT:mm		TOLERANCE ±0.5 mm		TITLE M8 2+3Pin Cable F Conn. F Pin		ITEM NO		DRAWN BY Mila		DATE 2014-01-09	
SCALE 2:1		SIZE A4		SHEET 1 OF 1		DWG NO 8H-05AFFM-SR7AXX		CHECKED BY Jimmy		DATE 2014-01-09	
REV. A		WC-REV. A.2		① Inspection item		CUSTOMER ALTW		APPROVED BY Jerry		DATE 2014-01-09	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8H-05AFFM-SR7A01](#)