




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION




Cable ② 8HP-05AFFM-QL5000 ①
Color: Black

8HP-05AFFM-QL5AXX
XX: 01~99Meters
01: 01Meter
02: 02Meter
...
99: 99Meters
Cable Length(L): 01~99Meters



Note:
* ① Important Dimension.
* Waterproof Rate: IP65.
* Connector: PU, Black.
* Female Pin: Copper Alloy, Gold Plated.
* Cable: UL2464 24AWG*5C+Talcum, PVC Jacket, UV Resistant, OD=5.0, Black.
* Cable Length Tolerance: 01M: ±40mm
02~05M: ±60mm
06~10M: ±100mm
11~30M: ±200mm
31~99M: ±500mm



Pin Assignments
Front View

5	Yellow 黃
4	Orange 橘
3	Red 紅
2	Brown 棕
1	Black 黑
Conn.	Wire Color

Pin Out

UNIT:mm		TITLE
TOLERANCE ±0.5 mm		
M8 5Pin Cable F Conn. F Pin		
SCALE 2:1	SIZE A4	SHEET 1 OF 1
REV. A	WC-REV. A.1	① Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Mila	2013-11-22
8HP-05AFFM-QL5AXX	CHECKED BY	DATE
CUSTOMER	Jimmy	2013-11-22
ALTW	APPROVED BY	DATE
	Jerry	2013-11-22

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8HP-05AFFM-QL5A01](#)