



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-920494~497	2009/02/24	Vicky	Update the drawing.
C	LEN1650534~537	2016/05/16	Vicky	Update Logo




8P-03AMMM-SL7BXX
 XX:01~99Meters
 01:01Meter
 02:02Meters
 :
 :
 99:99Meters
 Cable Length(L):01~99Meters



Pin Assignments
Front View

4	Black	黑
3	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		



Note:

* @@ Important Dimension.

* Waterproof Rate:IP67.

* Connector:PU,Black.

△* Male Pin:Copper Alloy,Gold Plated.

* Cable:22AWG*3C+Insulation,Black, PU,OD=4.5mm.

△* Cable Length Tolerance: 01M:±40mm
 02M~05M:±60mm
 06M~10M:±100mm
 11M~30M:±200mm
 31M~99M:±500mm

UNIT:mm		TITLE	M8 Conn	
TOLERANCE			Cable Screw 3P M Conn M Pin	
±0.5 mm		SCALE	Free	SHEET 1 OF 1
REV.	C	SIZE	A4	QC :Inspection Item

Amphenol LTW
 安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8P-03AMMM-SL7B01](#) [8P-03AMMM-SL7B02](#) [8P-03AMMM-SL7B05](#) [8P-03AMMM-SL7B10](#)