





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-920538~541	2009/02/24	Vicky	Update the drawing.
C	LEN1650539~542	2016/05/16	Vicky	Update Logo



8P-04AMMM-SL7AXX
XX:01~99Meters
01:01Meter
02:02Meters
:
:
99:99Meters
Cable Length(L):01~99Meters

- Note:
- * @C Important Dimension.
 - * Waterproof Rate:IP67.
 - * Connector:PU,Black.
 - * Male Pin:Copper Alloy,Gold Plated.
 - * Cable:UL2464 22AWG*4C+Talcum,Black, PVC Jacket,UV Resistant,OD=5.0mm.
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



Pin Assignments
Front View

4	Black	黑
3	Blue	藍
2	White	白
1	Brown	棕
Conn.	Wire Color	
Pin Out		

UNIT:mm				TITLE M8 Conn Cable Screw 4P M Conn M Pin SCALE Free SHEET 1 OF 1 REV. C SIZE A4 QC :Inspection Item			Amphenol LTW 安費諾亮泰企業股份有限公司			ITEM NO			DRAWN BY Vicky			DATE 2016/05/16					
TOLERANCE ±0.5 mm										DWG NO 8P-04AMMM-SL7AXX			CHECKED BY Rita			DATE 2016/05/16					
										CUSTOMER ALTW			APPROVED BY Lisa			DATE 2016/05/16					
1		2		3			4			5			6			7			8 FMW0702-01-01A		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8P-04AMMM-SL7A01](#) [8P-04AMMM-SL7A02](#) [8P-04AMMM-SL7A05](#) [8P-04AMMM-SL7A10](#)