




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-920547~550	2009/02/24	Vicky	Update the drawing.
C	LEN1630329~332	2016/03/09	Vicky	Update Logo



Note:

- * @ Important Dimension
- * Waterproof Rate: IP67
- * Connector: PU, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 22AWG*4C+Talcum, Black, PVC Jacket, UV Resistant, OD=5.0mm
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



4	Black	黑
3	Blue	藍
2	White	白
1	Brown	棕
Conn.	Wire Color	
	Pin Out	

UNIT:mm		TITLE	M8 Conn
TOLERANCE			Cable Screw 4P M Conn M Pin
±0.5 mm		SCALE	Free
		SHEET	1 OF 1
REV. C	SIZE A4	QC	Inspection Item

Amphenol LTW		ITEM NO	DRAWN BY	DATE
安費諾亮泰企業股份有限公司		DWG NO	Vicky	2016/03/09
		CUSTOMER	Rita	2016/03/09
			Lisa	2016/03/09

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8P-04AMMM-SR7A01](#) [8P-04AMMM-SR7A02](#) [8P-04AMMM-SR7A05](#) [8P-04AMMM-SR7A10](#)