






THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-920316~319	2009/02/12	Vicky	Update the drawing.
C	LEN1510288~291	2015/01/07	Sam	Update logo.



Conn.

8P-04BFFM-SR7AXX
XX: 01~99Meters
01: 01Meter
02: 02Meters
.....
99: 99Meters
Cable Length(L): 01~99Meters



Pin Assignments
Front View

4	Black	黑
3	Blue	藍
2	White	白
1	Brown	棕
Conn.	Wire Color	
Pin Out		

- Notes:
- * $\varnothing$ Important Dimension.
 - * Waterproof Rate: IP67.
 - * Connector: PU, Black.
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Cable: UL2464 22AWG*4C+Talcum, Black, PVC Jacket, UV Resistant, OD=5.0mm.
 - * Cable Length Tolerance: 01M: ± 40 mm
02M~05M: ± 60 mm
06M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm

UNIT:mm			TITLE			M8 Conn				
TOLERANCE			Cable Screw 4P F Conn F Pin							
±0.5 mm			SCALE	3:2	SIZE	A4	SHEET	1	OF	1
			REV.	C	WC-REV.	A.1	QC: Inspection item			

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Sam	2015-01-07
CUSTOMER	Vicky	2015-01-07
ALTW	Rita	2015-01-07

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8P-04BFFM-SR7A01](#) [8P-04BFFM-SR7A02](#) [8P-04BFFM-SR7A05](#) [8P-04BFFM-SR7A10](#)