


NOTES:

1. MATERIALS AND FINISHES:
 HD-BNC STR PLUG - BeCu, NICKEL PLATING
 CABLE - BELDEN 1855A
2. ELECTRICAL:
 A. IMPEDANCE: 75 OHM
3. PACKAGING:
 A. QUANTITY: SINGLE PACK
 B. MARKING: BAG TO BE MARKED
 "AMPHENOL RF, 95-850-158XXXX AND DATE CODE".

THIRD ANGLE PROJ.

REVISIONS

| REV | DESCRIPTION | DATE | ECO | APPR |
|-----|---|-----------|-------|--------|
| A | RELEASE TO MFG | 15-May-15 | 50370 | NR/BCG |
| B | HST REMOVED | 30-Jun-15 | 50581 | NR/BCG |
| C | HST ADDED LENGTH TABLE & FORMAT UPDATED | 25-Oct-18 | 9489 | KR |



| LENGTH TABLE | | | |
|------------------------|----------------------|-------------------------------|-----------------------------------|
| PART NUMBER (IMPERIAL) | PART NUMBER (METRIC) | LENGTH 'L' IN INCHES [METERS] | LENGTH 'X' IN INCHES [METERS] MIN |
| 95-850-158-006 | - | 6.00 [0.152] | 0.75 [0.019] |
| | 95-850-158M025 | 9.84 [0.250] | |
| 95-850-158-012 | - | 12.00 [0.305] | |
| 95-850-158-018 | - | 18.00 [0.457] | 1.50 [0.038] |
| | 95-850-158M050 | 19.69 [0.500] | |
| 95-850-158-024 | - | 24.00 [0.610] | |
| | 95-850-158M075 | 29.53 [0.750] | |
| 95-850-158-036 | - | 36.00 [0.914] | |
| | 95-850-158M100 | 39.37 [1.000] | |
| 95-850-158-048 | - | 48.00 [1.219] | |
| | 95-850-158M200 | 78.74 [2.000] | |
| | 95-850-158M300 | 118.11 [3.000] | |
| | 95-850-158M400 | 157.48 [4.000] | |
| | 95-850-158M500 | 196.85 [5.000] | |

| TOLERANCE TABLE | |
|---------------------------------|----------------|
| LENGTH IN INCHES/FT [METERS] | TOLERANCE |
| 0" - 23.90" [0 - 0.607] | ±0.25" [0.006] |
| 24.00" - 59.00" [0.610 - 1.499] | ±0.50" [0.013] |
| 5.0' - 24.9' [1.524 - 7.617] | ±2.5% |
| 25.0' & UP [7.620 & UP] | ±5.0% |

DESIGN REQUIREMENTS:

- | | |
|--|--|
| <input checked="" type="checkbox"/> FREQUENCY : DC - 3 GHz | <input checked="" type="checkbox"/> CONTINUITY |
| <input type="checkbox"/> VSWR :----- MAX | <input checked="" type="checkbox"/> HI-POT: 500 VRMS |
| <input type="checkbox"/> INS. LOSS ----- dB MAX | <input type="checkbox"/> OTHER |

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

| | | | | | |
|---|------------------------------|-------------|-----------|---|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES ±.015 (0.381 mm) ±.005 (0.127 mm) ± 1° | MATERIAL | DRAWN | DATE | TITLE HD-BNC STR PLUG TO HD-BNC STR PLUG USING BELDEN 1855A CABLE VARIOUS LENGTHS | Amphenol RF www.amphenolrf.com |
| | SEE NOTES | RAJAGOPAL N | 09-Dec-14 | | |
| NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data. | REFERENCE | ENGINEER | DATE | SCALE: 1.8:1.0 | DRAWING NO. 95-850-158XXXX ITEM NO. 95-850-158XXXX PART NO. 95-850-158XXXX |
| | EAR # 6513 | RAJAGOPAL N | 09-Dec-14 | SHEET 2 OF 2 | |
| | CONFIGURATION LEVEL: In Work | APPROVED | DATE | | DWG SIZE |
| FINISH | K. CAPOZZI | 25-Oct-18 | | B | C |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[095-850-158-012](#) [095-850-158-024](#) [095-850-158-018](#) [095-850-158-048](#) [095-850-158-006](#) [095-850-158M400](#) [095-850-158M075](#) [095-850-158M200](#) [095-850-158M100](#) [095-850-158-036](#) [095-850-158M050](#) [095-850-158M025](#)