

NOTES:


1. MATERIALS AND FINISHES:  
 N STR PLUG IP 67 - BRASS, NICKEL PLATING  
 CABLE - LMR 400
2. ELECTRICAL:  
 A. IMPEDANCE: 50 OHM

3. PACKAGING:  
 A. QUANTITY: SINGLE PACK  
 B. MARKING: BAG TO BE MARKED  
 "AMPHENOL RF, 95-909-173-XXX AND DATE CODE"


THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	12-Feb-19	10464	VR
B	NO CHANGE TO THIS SHEET	20-Mar-19	10943	PL
C	NO CHANGE TO THIS SHEET	09-Apr-19	11201	SK



LENGTH TABLE		
PART NUMBER (IMPERIAL)	PART NUMBER (METRIC)	LENGTH 'L' IN INCHES [METERS]
95-909-173-006	-	6.00 [0.152]
-	95-909-173M025	9.84 [0.250]
95-909-173-012	-	12.00 [0.305]
95-909-173-018	-	18.00 [0.457]
-	95-909-173M050	19.69 [0.500]
95-909-173-024	-	24.00 [0.610]
-	95-909-173M075	29.53 [0.750]
95-909-173-036	-	36.00 [0.914]
-	95-909-173M100	39.37 [1.000]
95-909-173-048	-	48.00 [1.219]
-	95-909-173M150	59.06 [1.500]
95-909-173-072	-	72.00 [1.829]
-	95-909-173M200	78.74 [2.000]
95-909-173-096	-	96.00 [2.438]
95-909-173-108	-	108.00 [2.743]
-	95-909-173M300	118.11 [3.000]
95-909-173-120	-	120.00 [3.048]
-	95-909-173M400	157.48 [4.000]
95-909-173-240	-	240.00 [6.096]
95-909-173-360	-	360.00 [9.144]
-	95-909-173MI0L	393.70 [10.000]
95-909-173L050	-	600.00 [15.240]
-	95-909-173M20L	787.40 [20.000]
95-909-173L075	-	900.00 [22.860]
-	95-909-173M30L	1181.10 [30.000]
95-909-173L100	-	1200.00 [30.480]



SCALE 0.300

TOLERANCE TABLE	
LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

DESIGN REQUIREMENTS:

- FREQUENCY DC - 6 GHz       CONTINUITY
- VSWR: \_\_\_\_\_ : 1 MAX.       HI-POT: 750 VRMS
- INS. LOSS: \_\_\_\_\_ dB MIN.       OTHER

**CUSTOMER OUTLINE DRAWING**  
 ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL      3 PLACE DECIMAL      ANGLES ±.015 (0.381 mm)      ±.005 (0.127 mm)      ± 1°	MATERIAL	DRAWN	DATE	TITLE N STR PLUG IP 67 TO N STR PLUG IP 67 USING LMR 400 CABLE VARIOUS LENGTH		Amphenol RF www.amphenolrf.com	
	SEE NOTES	VIJAY N M	29-Jan-19				
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE	ENGINEER	DATE	DRAWING NO. 95-909-173-XXX ITEM NO. 95-909-173-XXX		PART NO. 95-909-173-XXX	
	EAR # 8886	VIJAY N M	29-Jan-19				
	CONFIGURATION LEVEL: In Work	APPROVED	DATE	SCALE: 1.0:1.0	SHEET 2 OF 2	DWG SIZE	REV
FINISH	K.CAPOZZI	09-Apr-19	B	C			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

[095-909-173M100](#) [095-909-173-036](#) [095-909-173-072](#) [095-909-173M30L](#) [095-909-173-108](#) [095-909-173-120](#) [095-909-173L100](#) [095-909-173-240](#) [095-909-173-012](#) [095-909-173-360](#) [095-909-173M150](#) [095-909-173M400](#) [095-909-173-024](#) [095-909-173M075](#) [095-909-173-048](#) [095-909-173M20L](#) [095-909-173M300](#) [095-909-173M025](#) [095-909-173L075](#) [095-909-173M050](#) [095-909-173-018](#) [095-909-173L050](#) [095-909-173M200](#) [095-909-173-006](#) [095-909-173M10L](#) [095-909-173-096](#)