



- *  Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black.
- * Male Pin: Copper Alloy, Gold Plated.
- * Cable: UL2464 20AWG+D+AL/My
PVC Jacket UV Resistant, Black.
- * Cable Length Tolerance: 01M:40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

ABB-XXAFMM-LL7AXX

02: 2Pin ———— ↑

03: 3Pin

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
:
99 : 99Meters

Cable Length(L):01~99Meters

3P	PVC	5.0	20	ABB-03AFMM-LL7AXX
2P		5.8		ABB-02AFMM-LL7AXX
Contacts	Cable Jacket	Cable OD	AWG	Item No.

UNIT : mm	
TOLERANCE ± 0.5	

TITLE		STANDARD CABLE LOCK F CONN M PIN	
SCALE	1 : 2	SIZE	A4
REV.	A	SHEET	OF
		WC-REV.	A.
			QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Mafei	DATE 2017-06-24
DWG NO ABB-XXAFMM-LL7AXX	CHECKED BY Jerry	DATE 2017-06-24
CUSTOMER ALTW	APPROVED BY Max	DATE 2017-06-24

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ABB-03AFMM-LL7A02](#)