




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Conn.




ABB-XXAFMM-SL7AXX


02: 2Pin
:
03: 3Pin

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
99 : 99Meters

Cable Length(L): 01~99Meters

3 Yellow 黃	2 Red 紅
2 White 白	1 Green 綠
1 Black 黑	
Pin # Wire	Pin # Wire

Pin Out



3 Pin 2 Pin

Pin Assignments Front View

3P	PVC	5.0	20	ABB-03AFMM-SL7AXX
2P		5.8		ABB-02AFMM-SL7AXX
Contacts	Cable Jacket	Cable OD	AWG	Item No.

- Note:
- * (CC) Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black.
 - * Male Pin: Copper Alloy, Gold Plated.
 - * Cable: UL2464 20AWG+D+AL/My
PVC Jacket UV Resistant, Black.
 - * Cable Length Tolerance: 01M: 40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT: mm

TOLERANCE ±0.5

TITLE STANDARD CABLE SCREW F CONN M PIN			
SCALE 1:2	SIZE A4	SHEET 1 OF 1	
REV. A	WC-REV. A.1	(CC): Inspection item	

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO.	DRAWN BY Mafei	DATE 2017-06-24
DWG NO. ABB-XXAFMM-SL7AXX	CHECKED BY Jerry	DATE 2017-06-24
CUSTOMER ALTW	APPROVED BY Max	DATE 2017-06-24

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ABB-03AFMM-SL7A01](#) [ABB-02AFMM-SL7A01](#)