




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



Conn.


4P	PVC	5.5	20	ABB-04BFFM-LL7AXX
3P		5.0		ABB-03BFFM-LL7AXX
2P		5.8		ABB-02BFFM-LL7AXX
Contacts	Cable Jacket	Cable OD	AWG	Item No.



4 White 白	3 Yellow 黃	2 Red 紅
3 Black 黑	2 White 白	1 Green 綠
2 Blue 藍	1 Black 黑	
1 Brown 棕		
Pin # Wire	Pin # Wire	Pin # Wire

ABB-XXBFFM-LL7AXX
02: 2Pin
04: 4Pin
XX : 01~99Meters
01 : 01Meter
02 : 02Meters
99 : 99Meters
Cable Length(L): 01~99Meters

Note:
* Important Dimension To Check.
* Waterproof Rate: IP67
* Housing: Nylon+GF, Black.
* Female Pin: Copper Alloy, Tin Plated.
* Cable: UL2464 20AWG+D+AL/My
PVC Jacket UV Resistant, Black.
* Cable Length Tolerance: 01M: 40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm



Pin Assignments Front View

UNIT:mm		TOLERANCE ±0.5		TITLE STANDARD CABLE LOCK F CONN F PIN		SCALE 1:1		SIZE A4		SHEET 1 OF 1		REV. A		WC-REV. A.2		QC: Inspection item		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Jinhai		DATE 2015-07-14	
DWG NO		ABB-XXBFFM-LL7AXX		CHECKED BY Rensong		DATE 2015-07-14		APPROVED BY Jerry		DATE 2015-07-14		CUSTOMER		ALTW		FMM10702-01-02A1									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ABB-02BFFM-LL7A02](#) [ABB-02BFFM-LL7A05](#) [ABB-02BFFM-LL7A10](#) [ABB-03BFFM-LL7A02](#) [ABB-03BFFM-LL7A05](#)
[ABB-03BFFM-LL7A10](#) [ABB-04BFFM-LL7A02](#) [ABB-04BFFM-LL7A05](#) [ABB-04BFFM-LL7A10](#)