
Conn.



ABB-XXBFMM-LL7000
Color: Black




Cable Length(L):01~99Meters

Note :

- * Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black.
- * Male Pin: Copper Alloy, Gold Plated.
- * Cable: UL2464 20AWG+D+AL/My
PVC Jacket UV Resistant, Black.
- * Cable Length Tolerance: 01M:40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



3 Pin



2 Pin

Pin Assignments Front View

3P	PVC	5.0	20	ABB-03BFMM-LL7AXX
2P		5.8		ABB-02BFMM-LL7AXX
Contacts	Cable Jacket	Cable OD	AWG	Item No.

UNIT : mm	
TOLERANCE	
± 0.5	

TITLE		STANDARD	
CABLE LOCK F CONN M PIN			
SCALE	1 : 1	SIZE	A4
REV.	A	SHEET	1 OF 1
		WC-REV.	A.1
			QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Jinhai	2015-07-14
DWG NO	CHECKED BY	DATE
ABB-XXBFMM-LL7AXX	Rensong	2015-07-14
CUSTOMER	APPROVED BY	DATE
ALTW	Jerry	2015-07-14

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ABB-02BFMM-LL7A02](#) [ABB-02BFMM-LL7A05](#) [ABB-02BFMM-LL7A10](#) [ABB-03BFMM-LL7A02](#) [ABB-03BFMM-LL7A05](#) [ABB-03BFMM-LL7A10](#) [ABB-02BFMM-LL7A04](#) [ABB-02BFMM-LL7A03](#)