



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Conn.




① ACB-XXAFFM-SL7000
Color: Black

② Cable

Contacts	Cable Jacket	Cable OD	AWG	Item No.
6P	PVC	6.5	20	ACB-06AFFM-SL7AXX
5P		6.0		ACB-05AFFM-SL7AXX
4P		5.5		ACB-04AFFM-SL7AXX

Pin # Wire	Pin # Wire	Pin # Wire
6 Gray 灰	5 Green 綠	4 White 白
5 Yellow 黃	4 White 白	3 Black 黑
4 Green 綠	3 Black 黑	2 Blue 藍
3 White 白	2 Blue 藍	1 Brown 棕
2 Blue 藍	1 Brown 棕	
1 Brown 棕		




Pin Assignments Front View

ACB-XXAFFM-SL7AXX

04: 4Pin
06: 6Pin

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
99 : 99Meters

Cable Length(L): 01~99Meters



- Note:
- * ⌀ Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black.
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Screw Nut: Nylon+GF, Black.
 - * Cable: UL2464 20AWG+D+Al/My
 - * PVC Jacket UV Resistant, Black.
 - * Cable Length Tolerance: 01M: 40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm		TITLE
TOLERANCE	±0.5	MIDDLE CABLE SCREW F CONN F PIN
REV.	A	WC-REV. A.1
SCALE	1:1	SIZE A4
SHEET	1	OF 1
QC	Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE
ALTW	Jinhai	2015-07-16
	Rensong	2015-07-16
	Jerry	2015-07-16

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

<u>ACB-04AFFM-SL7A02</u>	<u>ACB-04AFFM-SL7A05</u>	<u>ACB-04AFFM-SL7A10</u>	<u>ACB-05AFFM-SL7A02</u>	<u>ACB-05AFFM-SL7A05</u>
<u>ACB-05AFFM-SL7A10</u>	<u>ACB-06AFFM-SL7A02</u>	<u>ACB-06AFFM-SL7A05</u>	<u>ACB-06AFFM-SL7A10</u>	